



Beige, Brown, Gray, Granite, Silver, Pearl White, Charcoal, Sandy Brown

Available colors

Cobalt+ stays behind the scenes thanks to its small size and natural colors that are designed to blend with most skin and hair tones. Eight standard colors are available, and your hearing health professional can even change the colored case anytime based on your preferences.



For over 50 years, Rexton has listened to the unique needs of Hearing Health Professionals and people with hearing loss around the world. Rexton develops a full line of solutions for all types of hearing loss and lifestyle needs with value, innovation, quality, and usability in mind. We strive to put our customers first at every opportunity and to make better hearing more accessible to all people.

www.rexton-online.com
www.rexton.com

Rev. 4/10 PN 10535157/a



[Cobalt+]

Now more than ever, good things come in small packages.



Now more than ever, good things come in small packages.

Introducing the new Cobalt+, with understated good looks and an exciting new bundle of high-tech features. The tiny Cobalt+ packs a powerful punch with technology that's sure to please even the most demanding and on-the-go wearer.

Features vary by product level. Talk to your hearing health professional for a complete feature list and to determine which product is right for you.

REXTON

www.rexton.com

REXTON



Comfort

Today's most advanced comfort features are cleverly hidden inside the tiny Cobalt+.

NEW! Feedback Preventer

Cobalt's Feedback Preventer uses proven technologies that stop feedback in its tracks, before you or anyone nearby can hear it.

NEW! Sound Radiance

Great for anyone that appreciates listening to music or simply wants the most brilliant sound possible, Sound Radiance enhances the perception of high frequency sounds. The result is sound that's fuller and richer.

Sound Locator

Rexton products equipped with Sound Locator mimic the outer ear's ability to help you find the sources of sound easily for the greatest sense of confidence, increased safety, and the most natural hearing experience.

SoundSmoothing®

Give yourself the ultimate in sound comfort with SoundSmoothing, a unique feature that can identify unpredictable sounds quickly and soften them without affecting speech understanding.

Speech

Better hearing never goes unnoticed, but the tiny Cobalt+ will.

Experience better hearing without drawing attention to yourself. Cobalt+ now has the newest technology for speech understanding, even if the sound is coming from behind you.

NEW! Focus 360

Focus 360° goes beyond the capabilities of traditional directional microphones. Now you can clearly hear and understand the important sounds of speech even when they come from someone sitting behind you in a car or walking alongside, all automatically.

Automatic Multi-channel Adaptive Directional Microphone

Achieve the best possible speech understanding automatically in very complex listening environments involving multiple speakers and other noise.

Automatic Noise Reduction

This technology improves listening comfort by softening distracting background noise and enhancing important speech all without requiring you to make adjustments.



Convenience

Cobalt+ is easy to handle and inconspicuous.

Blu Link Technology

Connect to your everyday electronic devices effortlessly. This cutting edge technology features **Bluetooth®** wireless connectivity, enabling you to easily connect your hearing instruments to your mobile phone, stereo, TV, and more using the optional, state-of-the-art Blu RCU.



Green & Easy

Developed with convenience in mind, Green & Easy technology allows Cobalt+ to be charged overnight using a handy charging unit for a full day of trouble-free operation. The charger also includes a drying function that leaves instruments dry and refreshed each morning for greater reliability.

Wireless Assistant

Rexton's Wireless Assistant provides both optimized sound quality as well as unmatched ease of use for binaural hearing systems. Key processing elements are automatically synchronized, and there's no guesswork for you since certain controls can be linked to allow easier handling.

Set & Go

Fiddling with hearing aid controls isn't exactly discreet. Cobalt+ makes these hassles history with technology that does all the work, automatically.

Automatic Environment Management

This technology assesses the listening situation and classifies it quickly and automatically. Based on the environment, the needed features are engaged to help you overcome the challenges you would most likely face in those situations.

Better hearing should be easy.

Automatic Equalizer

The Automatic Equalizer optimizes frequency response and sound impression based on the listening environment. Even less need for manual hearing aid adjustments to change listening programs results in easier wearing.

Cobalt+ and Blu RCU

With Rexton's Blu Link technology, Cobalt+ will help you stay connected to TV and movies, friends and family, music and more.

Blu RCU

Using **Bluetooth** technology, the Blu RCU streams high quality audio from all your favorite high-tech gadgets to any Rexton instruments with Blu Link technology. With the pre-paired transmitter, you can connect to any media device, hassle-free.

Blu RCU doubles as a remote control, allowing volume, treble and direct program changes at the touch of a button.



Mobile phone

You won't have to worry about missing another phone call. Instead, you can enjoy phone conversations directly through your hearing instruments, in both ears.



TV

With the help of Blu RCU, enjoy TV programs and movies with friends at home. Stream sound from the television with no audible delay and listen at a level that's most comfortable for you.

Music

Experience the joy of music again with Blu RCU. Send your favorite tunes wirelessly from your MP3 player or stereo right to your Rexton hearing aids.



The Bluetooth® word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by Siemens AG is under license. Other trademarks and trade names are those of their respective owners.